## Hubbellock® Devices

**60 Ampere, 600 Volts AC** 3 Pole, 4 Wire Grounding and 4 Pole, 5 Wire Grounding

## **Plugs and Flanged Inlets**





\_4.81"\_ (122.2) HBL26519

**IP30** 





**Plugs** 

Description	Cord Dia.	Catalog Numbers	
Black phenolic interior with yellow thermoplastic sleeve over steel housing.	.92"-1.45" (23.36-36.83)	HBL26419	-
Black phenolic interior with blue thermoplastic sleeve and steel housing.	1.00"-1.50" (25.40-38.10)	-	HBL26519



3.94" 4.13" (104.9) 2.69" (68.3) 3.50" (88.9)

HBL26522

## Flanged Inlets

Description	Catalog Numbers	
Black phenolic interior with steel housing and flange.	HBL26422	-
Black phenolic interior with steel housing and flange with blue finish.	-	HBL26522

