



WIRING DEVICE-KELLEMS

(/wiringdevice-  
kellems/en/myList)

(/wiringdevice-  
kellems/en/)

Home (/Wiringdevice-Kellems/En/) / Products (/Wiringdevice-Kellems/En/Products/CI/DataHub\_WebRoot\_WDK)  
/ Electrical & Electronic (/Wiringdevice-Kellems/En/Products/Electrical-Electronic/CI/535411\_WDK)  
/ Wiring Devices (/Wiringdevice-Kellems/En/Products/Electrical-Electronic/Wiring-Devices/CI/559793\_WDK)  
/ Industrial Connectivity And Control Products (/Wiringdevice-Kellems/En/Products/Electrical-Electronic/Wiring-Devices/Industrial-Connectivity-And-Control-Products/CI/2028554\_WDK)  
/ Control Connectors (/Wiringdevice-Kellems/En/Products/Electrical-Electronic/Wiring-Devices/Industrial-Connectivity-And-Control-Products/Control-Connectors/C/2028555\_WDK)  
/ HRFM03501

# HRMF03501

by multiple brands  
Catalog ID: HRFM03501



SHARE

Mini-Quick Control Connectors, Female Flanged Receptacle, 3P, 16/3

More Information

Where to Buy

Search Location

WHERE TO BUY

[Contact Us \(/contactUs\)](#)

## Overview ( )



## Product Details ( )



### General

|                |  |
|----------------|--|
| Construction   | Metallic Shell   |
| Item Type      | Female Receptacle  |
| Material       | Composite  |
| OEM Brand Name | Hubbell Wiring Device-Kellems  |
| Performance    | <ul style="list-style-type: none"> <li>Electrical - Amperage - #16 AWG - 2&amp;3P=15A, 4P=12A, 5&amp;6P=10A</li> <li>Electrical - Contact Resistance - Less than or equal to 5 Milliohm</li> <li>Electrical - Isolation Resistance - Greater than or equal to 1000 Megaohm</li> <li>Electrical - Voltage Rating - 600V DC/600V AC</li> <li>Environmental - Corrosion Resistance - 500 hours salt spray per MIL-STD-1344, Method 1001</li> <li>Environmental - Ingress Protection - IP66 Suitability</li> <li>Environmental - Moisture Protection - UL Type 4, 4X, 12 and 13</li> <li>Environmental - Operating Temperature - AWM2661 cables: -20°C to 105° C</li> <li>SEOOW cable: -40°C to 105° C</li> <li>Environmental - Vibration Resistance - 10 - 2,000 Hz @15g per MIL-STD-1344, Method 2005</li> </ul> |
| UPC            | 783585837116   |

### Current Related

|                |      |
|----------------|------|
| Current Rating | 15   |
| Wattage        | 9000 |

### Conductor Related

|                |        |
|----------------|--------|
| Conductor Type | Copper |
|----------------|--------|

### Certifications and Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li> <li>UL 2238 and UL50E, File No. E192071</li> </ul> |
|----------------------|---|

## Resources / Downloads ( )



### WHERE TO BUY



### SUPPORT



### OUR COMPANY



### SALES CORNER





(/wiringdevice-  
kellems/en/)

Wiring Device - Kellems is a proud member of the Hubbell family.

[Click to learn more.](#)

© 2017 Hubbell. All Rights Reserved

[Privacy Policy \(/hubbell/en/terms-of-use#99\)](#)

[Terms of Use \(/hubbell/en/terms-of-use\)](#)



(<https://twitter.com/HUBBELLELECSYS>) (<https://www.youtube.com/user/HubbellElectricalSys>)