

HBL14W47 -- Straight Blade Products, Elastogrip Series Plug



2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow Elastomer, Watertight

Product Specifications

Product Type	 Plugs
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3-Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Elastogrip
Enhancement	Water Tight
Color	 Yellow
NEMA No.	5-15P
Horsepower	0.5
Cord Dia.	.300"-.655" (7.6-16.6)
Type	2 Pole, 3 Wire, Grounding
Rating	15A,125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP55
Housing Material	PVC-Yellow
Blade Holder Material	Nylon-Natural
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Yellow
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Copper Alloy
Terminal Screw Material	#8-32 Brass /Ni plated for neutral
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#12 AWG copper stranded conductor
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
UPC Number	783585013008
Weight in LBs	0.200
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

