




HBL5969VY -- Straight Blade Products, Valise Connector Body



2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow Nylon

Product Specifications

Product Type	 <p>Connectors</p>
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3-Wire Grounding
Wiring Method	Back Wire
Hospital Grade ?	No
Plug/Connector Grade	Valise
Color	 <p>Yellow</p>
NEMA No.	5-15R
Cord Dia.	.220"-.660" (5.6-16.8)
Type	2 Pole, 3 Wire, Grounding
Rating	15A, 125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	Nylon
Cord Clamp Material	Noryl
Terminal Screw Material	#8-32 Steel (copper or nickel finish)
Ground Screw Material	#8-32 Steel, (green finish)
Power Contacts Material	.040" (1.0) Phosphor Bronze
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#12 AWG copper stranded conductor
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
Certified	UL2305 OEM and replacement use on convention center flat cable cord sets.
UPC Number	783585013107
Weight in LBs	0.100
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



NEMA Configuration

