

# HBL21414B -- Hubbellock Connector Body



3P4W, 30A 600V AC Max, Black Phenolic

HBL21414B

## Product Specifications

Product Type



Hubbellock  
Devices

Product Item	Connector Body
Wiring Scheme	3-Pole, 4-Wire Grounding
Multi-Rating	30A 600V AC, 20A 250V DC
Item Style	Standard
Device Color	Black/White
Cord Dia.	.630"-1.20" (16.0-30.5)
Housing Material	Black nylon
Cord Clamp Material	Rynite (white)
Terminal Screw Material	Steel pressure screw- zinc plate
Ground Screw Material	Steel pressure screw- zinc plate
Cord Clamp Screw Material	Steel-zinc-plated
Body Holding Screw Material	Steel-zinc-plated
Body Contact Carrier Material	Black Rynite
Contact Spring Material	.032" (.8) Bronze
Ground Contact Material	.032" Bronze
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	20A #12AWG; 30A #10AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP30
Listings	UL/CSA
UPC Number	783585017297
Weight in LBs	1.05
Link to Drawing Library	<a href="#">Click here for Library</a>
Link to PDF Catalog	<a href="#">Click here for Catalog</a>

