

HBL21415B -- Hubbelock Plug



3P4W, 30A 600V AC Max, Black Phenolic

HBL21415B

Product Specifications

Product Type	 <p>Hubbelock Devices</p>
Product Item	Plug
Wiring Scheme	3-Pole, 4-Wire Grounding
Multi-Rating	30A 600V AC, 20A 250V DC
Item Style	Standard
Device Color	Black/White
Cord Dia.	.630"-1.20" (16.0-30.5)
Blade Holder Material	Black Thermoset
Housing Material	Black nylon
Cord Clamp Material	Glass Reinforced PET
Blade Material	Brass
Terminal Screw Material	Copper lug terminals with steel set screws
Ground Screw Material	Copper lug terminals with steel set screws
Cord Clamp Screw Material	Stainless steel, Multi-drive
Body Holding Screw Material	Stainless steel, Multi-drive
Contact Spring Material	.032" (.8) Bronze
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	20A #12AWG; 30A #10AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP30
Listings	UL/CSA
UPC Number	783585017273
Weight in LBs	0.8
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

