HBL2821 -- Twist-Lock Plug



4P5W, 30A 3PH 277/480V AC, L22-30P, Black & White

Product Specifications

Product	Type
---------	------

Material



Product Item Plug 4-Pole, 5-Wire Grounding Wiring Scheme

Amperage 3 Phase Y 277/480V AC Voltage

NEMA Configuration L22-30P Item Style Insulgrip

Black/White **Device Color**

Horsepower

Cord Dia. .35"-1.15" (9-29)

Blade Holder Material Natural White Nylon

Terminal Retainer Clear polycarbonate

Housing Material Black nylon

Cord Clamp Material Natural (white) nylon

Blade Material Brass

Terminal Clamp Material .08" (2) steel-nickel plated

Terminal Screw Material #10-32 Brass (white finish on neutral screw when used) Multi-drive

#10-32 Brass (green finish) Multi-drive **Ground Screw Material**

Cord Clamp Screw Steel, zinc plated Multi-drive Material

Body Holding Screw

Steel, zinc plated Multi-drive Material

Ratings Molded In or Stamped On Permanently ink marked on product Catalog No

Dielectric Voltage

2,000V minimum Withstand **Current Interrupting** Certified for current interrupting at full rated current

Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power

Temperature Rise factor of .75. Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62,

CSA C22.2 No. 49.

30A #10 AWG **Terminal Accommodation**

Terminal Identification Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)

HB or better per UL 94 or CSA 22.2 No. 0.6 Flammability

Maximum Continuous 75 C Minimum -40 C (w/o impact) **Operating Temperatures**

Moisture Resistance IP20

Listings FED SPEC UL/CSA

UPC Number 783585039695

Weight in LBs

Cord Accommodation

Link to Drawing Library Click here for Library

Link to PDF Catalog Click here for Catalog



