


# HBL7484 -- Twist-Lock Connector Body



HBL7484

3P3W, 15A 125/250V, ML-3R, Nylon Body, Phenolic Base, Black

## Product Specifications

Product Type	 Twist-Lock Devices
Product Item	Connector Body
Wiring Scheme	3-Pole, 3-Wire Non-Grounding
Amperage	15A
Voltage	125/250V AC
NEMA Configuration	ML-3R
Item Style	Standard
Device Color	Black
Cord Dia.	.281-.421" (7.1-10.7)
Housing Material	Phenolic
Cord Clamp Material	Metallic
Cord Clamp Screw Material	Steel - black oxide
Body Holding Screw Material	Steel, zinc plated
Body Contact Carrier Material	Black Thermoset
Contact Spring Material	.031" Brass
Ground Contact Material	.031" (.8) Brass
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A #14 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	UL
UPC Number	783585237381
Weight in LBs	0.05
Link to Drawing Library	<a href="#">Click here for Library</a>
Link to PDF Catalog	<a href="#">Click here for Catalog</a>

