



HBL7485 -- Twist-Lock Plug



3P3W, 15A 125/250V, ML-3P, Nylon Body, Phenolic Base, Black

Product Specifications

Product Type	
Product Item	Plug
Wiring Scheme	3-Pole, 3-Wire Non-Grounding
Amperage	15A
Voltage	125/250V AC
NEMA Configuration	ML-3P
Item Style	Standard
Device Color	Black
Cord Dia.	.281"-.421" (7.1-10.7)
Blade Holder Material	Black Phenolic
Housing Material	Black nylon
Cord Clamp Material	Zinc Plated Black Steel
Blade Material	Brass
Terminal Screw Material	Brass
Ground Screw Material	Brass
Cord Clamp Screw Material	Steel zinc plated
Body Holding Screw Material	Steel zinc plated
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000 minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A #14 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	UL
UPC Number	783585237411
Weight in LBs	0.05
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



NEMA Configuration

