


HJ1012BPK25 -- Cord Connectors



Hubbell Juniors are a miniature liquidtight version of the full-sized Hubbell cord connectors. They feature the same GOTCHA® ring technology and neoprene bushings.

Product Specifications

Product Type	Cord Connectors
Material/Style	Nylon Miniature with Spiral
Cord Diameter Range	.20"-.27" (5.1-6.7)
Cord Connector Body Style	Straight Male
HUB Size	1/4"
Color	 Black
Effective Operating Temperature	-30°F to +225°F (-34°C to +107°C)
Recommended Knockout Hole Size	.53"-.54" (13.4-13.6)
Flammability	Hubbell Juniors have a UL 94-V2 rating.
Dimension A	.65" (16.5) Dia.
Dimension B	2.55" (64.8) Ref.
Dimension C	.40" (10.2)
Dimension D	.29" (7.4) Throat Dia.
Dimension E	.27" (6.9)
Dimension F A/C	.65" (16.5)
Dimension F A/F	.60" (15.2)
Certifications	UL Listed, CSA Certified
Packaging	Bulk 25
UPC Number	78358502303
Weight in LBs	0.35
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

