




Heyco® Dome Plugs

Mounting Hole Diameter Range: .187" (4,7 mm) to 6.000" (152,4 mm)

- Close unneeded panel holes and electrical knockouts.
- Quick and easy installation.
- Convex, matte finish head tapers to thin edge (Except DP-187).
- Multiple sizes for use in .187" (4,7 mm) to 6.000" (152,4 mm) diameter holes.
- Lock firmly into panel up to .250" (6,4 mm) thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Approximate Head Thickness: .062" (1,6 mm). Thickness may vary.
- For Snap-In Metric Dome Plugs see page 6-28.

MOUNTING HOLE DIAMETER in. mm.	PART NO.			DESCRIPTION	PART DIMENSIONS				
	Black	White	Colors xx**		A Head Diameter in. mm.		B Overall Height in. mm.		
Single Locking Step for Panel Thickness up to .062" (1,6 mm)									
.187 4,7	2590	2591	2592xx	DP 187*	.25	6,4	.23	5,9	
.250 6,4	2607 2603	2608 2604	2609xx 2605xx	DP 250-040† DP 250	.31	7,9	.31	7,9	
.312 7,9	2613	2614	2615xx	DP 312	.38	9,5			
Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)									
.375 9,5	2617	2618	2619xx	DP 375	.47	11,9	.41	10,3	
.437 11,1	2633	2634	2635xx	DP 437	.53	13,5			
.500 12,7	2643	2644	2645xx	DP 500	.56	14,2			
.562 14,3	2653	2654	2655xx	DP 562	.66	16,7			
.625 15,9	2663	2664	2665xx	DP 625	.72	18,2			
.687 17,4	2673	2674	2675xx	DP 687	.78	19,8			
.750 19,1	2683	2684	2685xx	DP 750	.92	23,4			
.812 20,6	2693	2694	2695xx	DP 812	.99	25,1			
.875 22,2	2703	2704	2705xx	DP 875	1.02	25,8	.45	11,5	
1.000 25,4	2713	2714	2715xx	DP 1000	1.20	30,6			
1.093 - 1.125 27,8 - 28,6	2723	2724	2725xx	DP 1093	1.22	30,9			
1.187 30,1	2733	2734	2735xx	DP 1187	1.33	33,8	.47	11,9	
1.250 31,7	2740	2741	2742xx	DP 1250	1.38	34,9			
1.375 34,9	2753	2754	2755xx	DP 1375	1.50	38,1			
1.500 38,1	2763	2764	2765xx	DP 1500	1.67	42,4			
1.750 44,5	2773	2774	2775xx	DP 1750	1.92	48,7			
2.000 50,8	2783	2784	2785xx	DP 2000	2.17	55,1			
Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)									
2.093 - 2.125 53,2 - 54,0	2403	2404	***	DP 2.093	2.34	59,9	.75	19,1	
2.250 57,2	2411	2412	2413xx	DP 2.25	2.48	63,0	.75	19,1	
2.500 63,5	2790	2791	2792xx	DP 2.5	2.71	68,8			
3.000 76,2	2455	2456	2457xx	DP 3.0	3.16	80,3	.74	18,8	
3.375 85,7	2482	2483	***	DP 3.375	3.66	92,9	.75	19,1	
3.500 88,9	2464	2465	2466xx	DP 3.5	3.66	92,9			
4.000 101,6	2473	2474	2475xx	DP 4.0	4.17	105,8	.71	18,0	
5.000 127,0	2451	2452	***	DP 5.0	5.24	133,0	.75	19,1	
6.000 152,4	2453	2454	***	DP 6.0	6.22	157,9	.78	19,8	



Standard colors black and white. Consult Heyco for other colors (see below)
 *Convex, glossy finish head.

** xx indicates that, following the color match process, Heyco adds a two letter suffix to the Root Part No. shown. This suffix will identify your particular CUSTOM Color selection. Consult Heyco for molded nylon color chips for accurate matching. For details as well as information regarding our Stock Colors, see page 6-51.

***Consult Heyco for root Part No.
 † Max panel thickness is .040" (1,0 mm)

Quick Specs

Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories File E51579 Certified by the Canadian Standards Association File 8919
Flammability Rating	94V-2
Temperature Range	-40°F (-40°C) to 221°F (105°C)