



**International  
Components  
Corporation**

215 McCormick Dr.

Bohemia, New York 11716

Ph: (631) 952 - 9595 Fax: ( 631) 952 - 9597

E-mail: oemsales@icc107.com

## **MICRO-MINIATURE LOW PROFILE ROUND SPEAKER**

Contact Us



Product: MICRO-MINIATURE LOW PROFILE ROUND SPEAKER

Description: These Speakers Are Available, On A Special Order Basis, In 4, 16, 32, 45 And 100 Ohms.

Part Number: SR800RMS

### **SPECIFICATIONS**

FRAME DEPTH	4.2 mm
FRAME DIAMETER	20.0 mm
FREQUENCY RESPONSE	Fo ~ 5300
MATERIAL CONE/FRAME	MYLAR / PLASTIC
MEAN VALUE AT	1.2,1.5,2.0,2.5 KHz
MEASURED AT	0.1 W @ 0.5M
OUTPUT SOUND PRESSURE LEVEL (S.P.L)	71 ± 3 dB
RATED POWER WATTS Nom/Max	0.10 / 0.20
RESONANT FREQUENCY HZ WITOUT BAFFLE	800 ± 20%
ROHS COMPLAINT	YES
VOICE COIL IMPEDANCE	8 ± 15% @1.5KHz

215 McCormick Dr. Bohemia, New York 11716 , Telephone: (631) 952 - 9595, Fax:( 631) 952 - 9597