



[Previous Page](#)

[Printer Friendly Version](#)

Product: **PIEZO ELECTRIC ALARM WITH INTERNAL CIRCUITRY**
Description: **ROHS COMPLIANT**
Part Number: **BRP4222T-24-C**

SPECIFICATIONS:

RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	1 ~ 28 VDC
MAX CURRENT:	15 mA
SOUND OUTPUT LEVEL:	85dB @ 30CM
TERMINAL TYPE:	2 LUGS
RESONANT FREQUENCY:	2900 ± 500 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
TONE MODE:	CONTINUOUS
FRAME DIAMETER:	42.0 mm
FRAME DEPTH:	20.5 mm
MOUNTING DIMENSIONS:	10.0 mm

DIMENSIONS:

