



[Sign In/Register](#)

[HOME](#) [PRODUCTS](#) [SUPPORT](#) [ABOUT US](#) [NEWS](#) [CONTACT](#)

Part Number Search [SEARCH](#)

[HOME](#) [Industrial Components](#) [Switches & Pilot Devices](#) [CW Series](#) [CW4L-M1E10Q4PW](#)

Product Families

- Automation**
- Industrial Components**
- LED Lighting & Signaling**
- Machine Safety**
- Sensing**

**CW4L-M1E10Q4PW
Illuminated PB 22MM 1NO PW**



Key Features

- ø22.3mm mounting hole compliant with IEC 60947-5-1
- 3.5-mm operator travel for pushbuttons ensures comfortable and reliable operation
- Black and metallic bezels available
- Illuminated pushbuttons, pushbuttons, pilot lights, selector switches and key selector switches are available
- Direct opening NC contact
- 10A contact rating; up to three contact blocks for non-illuminated and two contact blocks for illuminated models can be connected
- Up to 6 contacts per switch
- UL Type 4X rating



Specifications Literature Downloads

Product Type	Illuminated Pushbutton
Mounting Hole Size	22mm
Shape	Round
Color	Pure White
Contact Rating	10A
Normally Open Contacts	1
Normally Closed Contacts	0
Ingress Protection Rating	IP65 degree of protection (IEC 60529) from panel front
Illumination Voltage	24VAC/DC
Lamp Type	LED
Operation Type	Momentary