

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

LW6S-2C6M
25mm Selector Switch



MSRP:

Key Features

- Projects only 2mm from front of the panel
- PCB, Solder Tab and Screw terminals available
- Metal or Plastic Bezels
- Gold (gold-clad silver) or Silver contacts
- Degree of Protection: IP65
- UL Recognized, CSA Certified and TUV Rheinland



Specifications	Literature	Downloads	Price and Availability
Product Type	Selector Switch		
Mounting Hole Size	Φ25mm		
Operation Type	Maintained		
Normally Open Contacts	2		
Normally Closed Contacts	2		
Shape	Round		
Number of Positions	2		