

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

HW1S-2TF11
22mm Selector Switch



Add to Cart

Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- UL Type 4X, IP65
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



Specifications

Literature

Downloads

Operation Type	Maintained
Product Type	Selector Switch
Mounting Hole Size	Φ22mm
Shape	Round
Normally Open Contacts	1
Normally Closed Contacts	1
Number of Positions	2