

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

FC6A-C24R1AE
24IO CPU 100-240VAC Relay



Add to Cart

Key Features

- Embedded Ethernet Port
- Embedded SD memory port
- Modbus TCP and RTU
- Embedded RS232C/RS485 user selectable
- Maximum 504 digital I/O
- Maximum 124 analog I/O
- Data Logging
- Web Server Functions
- Large programming and data memory
- cULus CE Class 1 Div 2



Specifications Literature Downloads Related

Product Type	CPU Base Module
Operating Voltage	100-240VAC
I/O Range	504
Ethernet Port	1st Embedded, 2nd Optional
Input Channels	14
Input Type	Sink/Source
Input Voltage	24VDC
Output	10
Output Type	Relay
I/O Expandable	15 Modules
USB Port	1 (Mini B-type)
Max Com Ports	2
SD Memory Slot	Embedded
Serial Port	RS232C/RS485 Selectable