

**Product Families**

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

**LF2B-C3P-ATHWW2-1M**  
LED BAR IP65 330mm 100-240VAC

Add to Cart



**Key Features**

- Input voltages either 100 - 240V AC or DC-battery compatible 12/24V DC
- Slim units: 40mm (w) x 29mm (h). Using mounting brackets, one-step installation in a narrow space is possible.
- Five Lengths (210/330/580/830/1,080mm) are offered to meet space requirements and illumination coverages.
- Bright and clear white LED illuminates the shapes and colors of target objects. (LF2B illuminance is approximately 25% higher than the LF1B.)
- Two covers: clear or white
- IP65 degree of protection (waterproof, dustproof), suitable for use in wet locations



\* UL applies for DC units only

Specifications

Literature

Downloads

Product Type	LED Illuminated Light Strip
Operating Voltage	100-240VAC
Color	Cool white
Cover/Lens	Clear cover
IP Rating	IP65
Length	330mm
Cable Length	1 m