

**Product Families**

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

**SV1H-07L-5**  
D Socket for RV 6-24V DC

Add to Cart

**Key Features**

- Class I, Division 2 and Class I, Zone 2 Hazardous Location options
- Lever for easy locking and removal of relay
- Solid State relay versions available
- Only 70mm in height from DIN rail
- Gold-plated contacts (RV8H-L & S and RV8H-2)
- Pre-assembled relay and DIN mount socket
- Universal screw terminals (flat and phillips) or spring clamp terminals available for all versions
- Universal AC/DC socket with built-in surge suppression and green LED
- 6A contact rating on 6mm RV8H, 8A on RV8H-2, 16A rating on RV8H-1
- Operating temperature of -40°C ~ 70°C for EMR (-20°C ~ +60°C for SSR)
- RoHS compliant



Specifications

Literature

Downloads

<b>Product Type</b>	Sockets (6-24V DC)
<b>Contact Rating</b>	6A
<b>Compatible IDEC Device</b>	RV1H-G-D5/D9/D12/D18/D24 (Relay)
<b>Terminal Type</b>	Screw