

**Product Families**

- ▶ **Automation**
- ▶ **Hazardous Location**
- ▶ **Industrial Components**
- ▶ **LED Lighting & Signaling**
- ▶ **Machine Safety**
- ▶ **Sensing**

## HS9Z-A52A Actuator Key Right Angle Type



**Add to Cart**

### Key Features

- World's smallest 4 contact solenoid interlock switch. (35 x 40 x 146 mm)
- Flexible installation - the head can rotate, allowing 8 different actuator entries
- Metal actuator entry slot ensures long life
- Standard 3m cable (1m and 5m cable available on request)
- Only proprietary actuators can be used, preventing unauthorized access (ISO14119, EN1088)
- 1000N min actuator locking strength (GS-ET-19)
- LED pilot light indicates the solenoid status
- Gold-plated contacts
- NC contacts are direct opening (IEC/EN60947-5-1)
- IP67 (IEC60529)
- B10d: 2.0E+06

**Specifications**

Literature

Downloads

Product Type

Accessories