

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

ASW2L20
22mm Selector Switch



MSRP: \$34.87

Add to Cart

Key Features

- Corrosion resistant octagonal chrome plated locking bezel
- Snap on 10A contacts
- Modular construction for maximum flexibility
- NEMA 4X and IP65 watertight/oiltight panel sealing
- Available assembled or as sub-components
- UL Listed, CSA Certified, TUV Approved, and CE Marked



Specifications Literature Downloads Price and Availability

Product Type	Selector Switch
Operation Type	Maintained
Mounting Hole Size	Φ22mm
Normally Open Contacts	2
Normally Closed Contacts	0
Shape	Round
Number of Positions	2