

**Product Families**

- ▶ [Automation](#)
- ▶ [Hazardous Location](#)
- ▶ [Industrial Components](#)
- ▶ [LED Lighting & Signaling](#)
- ▶ [Machine Safety](#)
- ▶ [Sensing](#)

## BAF111SNU BA Series Terminal Block



**MSRP:** \$6.97

[Add to Cart](#)

**Key Features**

- One piece construction, no end plates required
- Mount onto standard 35mm DIN rail
- Current capacities up to 40A on BA power blocks, 350A on BN power blocks
- UL94-V0 flammability rating
- BA power blocks available in 1 pole (15A, 20A, and 30A) or 3 pole (40A)
- BN power blocks available in 2, 3, or 4 pole (up to 350A)
- Fuse holders with optional blown fuse indication
- Optional dust covers and marking strips



**Specifications**

**Literature**

**Downloads**

**Price and Availability**

<b>Product Type</b>	One Piece Fuse Holder
<b>Current Rating</b>	10A
<b>Number of Poles</b>	1
<b>Terminal Screw</b>	M5
<b>Termination Type</b>	Screw
<b>Mounting Style</b>	DIN Rail
<b>Blown Fuse Indicator</b>	100-300V AC