

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

BAF111SU BA Series Terminal Block



MSRP: \$5.79

Add to Cart

Key Features

- One piece construction, no end plates required
- Mount onto standard 35mm DIN rail
- Current capacities up to 40A on BA power blocks, 350A on BN power blocks
- UL94-V0 flammability rating
- BA power blocks available in 1 pole (15A, 20A, and 30A) or 3 pole (40A)
- BN power blocks available in 2, 3, or 4 pole (up to 350A)
- Fuse holders with optional blown fuse indication
- Optional dust covers and marking strips



Specifications

Literature

Downloads

Price and Availability

Product Type	One Piece Fuse Holder
Current Rating	10A
Number of Poles	1
Terminal Screw	M6
Termination Type	Screw
Mounting Style	DIN Rail
Blown Fuse Indicator	None