

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

CW1K-2AE12
KeySelectorSW 22MM 2position

Add to Cart



Key Features

- ø22.3mm mounting hole compliant with IEC 60947-5-1
- 3.5-mm operator travel for pushbuttons ensures comfortable and reliable operation
- Black and metallic bezels available
- Illuminated pushbuttons, pushbuttons, pilot lights, selector switches and key selector switches are available
- Direct opening NC contact
- 10A contact rating; up to three contact blocks for non-illuminated and two contact blocks for illuminated models can be connected
- Up to 6 contacts per switch
- UL Type 4X rating



Specifications Literature Downloads

Product Type	Key Selector Switch
Mounting Hole Size	22mm
Shape	Round
Contact Rating	10A
Normally Open Contacts	1
Normally Closed Contacts	2
Ingress Protection Rating	IP65 degree of protection (IEC 60529) from panel front
Number of Positions	2 position
Key Removal	A
Operation Type	Maintained