


Product Families

- ▶ Automation
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

CW1L-M1E10Q4G
Illuminated PB 22MM 1NO G

MSRP:

Add to Cart



Key Features

- ø22.3mm mounting hole compliant with IEC 60947-5-1
- 3.5-mm operator travel for pushbuttons ensures comfortable and reliable operation
- Black and metallic bezels available
- Illuminated pushbuttons, pushbuttons, pilot lights, selector switches and key selector switches are available
- Direct opening NC contact
- 10A contact rating; up to three contact blocks for non-illuminated and two contact blocks for illuminated models can be connected



Specifications Literature Downloads Price and Availability

Product Type	Illuminated Pushbutton
Mounting Hole Size	22mm
Shape	Round
Color	Green
Contact Rating	10A
Normally Open Contacts	1
Normally Closed Contacts	0
Ingress Protection Rating	IP65 degree of protection (IEC 60529) from panel front
Illumination Voltage	24VAC/DC
Lamp Type	LED
Operation Type	Momentary

Description	File Type	File Size	Download
Sales Brochure	PDF	4,600K	Download
Catalog	PDF	4,600K	Download

Description	File Type	File Size	Download
3D CAD Drawings	ZIP	3,500K	Download
CAD Drawings	ZIP	205K	Download
Approval Certificate: CE	PDF	85K	Download
Approval Certificate: UL	PDF	85K	Download
Approval Certificate: CSA/cUL	PDF	117K	Download
Approval Certificate: TÜV	PDF	161K	Download
Approval Certificate: CCC	ZIP	439K	Download

You are not logged in.

If you are a registered user, please [Login Here](#) to view pricing and availability.

To register as a new user, [Click Here](#).