

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

FL1F-H12RCC SmartRelay CPU 100-20VAC-DC

Add to Cart

Key Features

- Embedded Ethernet Port
- Web Server Function
- Access using iOS and Android Apps
- Micro SD Memory slot
- Built-in Real Time Clock
- 10A Relay Outputs
- Optional Text Message Display panel
- Function block or Ladder programming
- Worldwide approvals
- cULus CE FM Class 1 Div 2 Lloyds Registered and ABS approved



Specifications Literature Downloads Related

Product Type	CPU Base Module
Operating Voltage	100-240 VAC/DC
I/O Range	60
Input Channels	8
Input Voltage	100-240 VAC/DC
I/O Expandable	10 modules
Output	4
Output Type	Relay
Ethernet Port	1 (RJ45)