

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

GT3A-6AD24
Timer 11-pin Plug-In DPDT 5A

Add to Cart

Key Features

- 4 selectable operation modes on each model
- External start, reset, and pause inputs
- Panel mount or socket mount
- Large variety of timing functions
- Power and output status indicating LEDs



Specifications

Literature

Downloads

Product Type	Multi Function Timer
Operating Voltage	24VAC 24VDC
Timer Type	Dry Contact Trigger (Momentary Start Signal)
Time Ranges	10 sec 1 sec 180 hrs 60 min 30 min 180 sec 60 sec 30 sec 18 sec 6 sec 3 sec 60 hrs 30 hrs 180 min 10 min 10 hrs
Timing Function	One Shot 1 (signal start) One Shot On Delay (signal start) Signal On/Off Delay 3 (signal start) One Shot 2 (signal start)
Contact Rating	5A
Contact Configuration	Delayed DPDT
Terminal Type	11 Pin Plug-In