

[Home](#) / [Products](#) / [Search Result](#)

CAT6 RJ-45 8P8C Modular Plugs

Products

- ▶ [Wire Termination](#)
- ▶ [Test & Measurement](#)
- ▶ [DataComm](#)
- ▶ [Tools & Totes](#)
- ▶ [Wire Management](#)
- ▶ [Wire Installation](#)
- ▶ [Mil-Aero Wire Processing](#)
- ▶ [OEM Connection Systems](#)
- ▶ [Electrical Supplies](#)



Product Resources

- [CAT 6 Modular Plugs Brochure](#)
 (PDF | 416K)
- [85-366 CAT 6 RJ-45 Modular Plug Instructions](#)
 (PDF | 182K | Rev 1)
- [TelCom Modular Plugs Wire Configuration Reference](#)
 (PDF | 22K)

Features

- 8 position, 8 contact RJ-45 modular plug compatible with CAT6 rated cables
- Three-piece design provides an easier assembly while maintaining optimal performance to pass CAT6 cabling standards and requirements in channel testing.
- Crimps with a standard RJ-45 crimp die ? not for use with tools with secondary strain relief crimp used with CAT 5e. (Not for use with the IDEAL Crimpmaster RJ-45 30-522 crimp tool)
- 50 micron gold contacts
- Suitable for solid or stranded, 23-24 AWG conductors
- Compatible with IDEAL crimp tools 30-696, 30-496, 33-700, 33-396

Models

Description	Catalog #
CAT6 RJ-45 Modular Plugs (8P8C), Pack of 25	85-366