
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANCON.



NOTES:

- 1. SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE
- 2. COVER MATERIAL: THERMOPLASTIC U.L. 94V-0
- 3. ALL DIMENSIONS ARE IN INCHES AND (MILLIMETERS)
- 4. TWO DEPRESSIONS ON COVERS FOR FIVE (5) CIRCUITS OR MORE
- 5. PARTS ARE SOLD AS "FUNCTIONAL ONLY".

PART NO.	NO. OF CIRCUITS	DIM. "A" IN. (MM)			
TC156F-2	2	.32 (8.1)			
TC156F-3	3	.47 (11.9)			
TC156F-4	4	.62 (15.8)			
TC156F-5	5	.78 (19.8)			
TC156F-6	6	.94 (23.8)			
TC156F-7	7	1.09 (27.7)			
TC156F-8	8	1.25 (31.7)			
TC156F-9	9	1.40 (35.7)			
TC156F-10	10	1.56 (39.6)			
TC156F-11	11	1.72 (43.6)			
TC156F-12	12	1.87 (47.5)			
TC156F-13	13	2.03 (51.5)			
TC156F-14	14	2.18 (55.5)			
TC156F-15	15	2.34 (59.4)			
TC156F-16	16	2.50 (63.4)			
TC156F-17	17	2.65 (67.4)			
TC156F-18	18	2.81 (71.3)			
TC156F-19	19	2.96 (75.3)			
TC156F-20	20	3.12 (79.2)			
TC156F-21	21	3.28 (83.2)			
TC156F-22	22	3.43 (87.2)			
TC156F-23	23	3.59 (91.1)			
TC156F-24	24	3.74 (95.1)			

* SEE NOTE 1



									C O N N E www.pancon.de / GER www.panconconnecto	RMANY	Bolingbrook, Illinoi	s	
									THF	MAS-CON , .156" THRU CIRCUIT SOCKET COVER			
									DIMENS	LESS OTHERWISE SPECIFIED, UNLESS OTHE ENSIONAL TOLERANCES ARE: IFIED, ALL DI			
										(.XXX) ± 02(. 5.) NGLES ±	ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.		
11	7/26 /11	KLR		REMOVED DIMENSIONS					DDU DRAWN BY	MAT'L	2:1		
10	9/28 /05	ΚI		Added RoHS compliant	2162				7-23-86	SEE NOTE 2	KA-10017	DWG.	
REV	DATE	BY	снк	DESCRIPTION	CN	- R	CUST	SUP	CH K'D WJH		KA-10017	SIZE	