

Ledex® Low Profile Size 1EC — Push or Pull

Size 1EC Medium Stroke, Conical Face
Part Number: 123421-0XX

All catalog products manufactured after
April 1, 2006 are RoHS Compliant

Performance

Maximum Duty Cycle	100%	50%	25%	10%
Maximum ON Time (sec) when pulsed continuously ¹	∞	100	36	7
Maximum ON Time (sec) for single pulse ²	∞	162	44	8
Watts (@ 20°C)	5	10	20	50
Ampere Turns (@ 20°C)	340	480	680	1075

Coil Data

awg (0XX) ³	Resistance (@20°C)	# Turns ⁴	VDC (Nom)	VDC (Nom)	VDC (Nom)	VDC (Nom)
25	0.83	140	2.1	2.9	4.1	6.5
26	1.38	186	2.6	3.7	5.2	8.2
27	1.91	210	3.2	4.5	6.3	10.1
28	3.17	273	4.1	5.7	8.1	12.8
29	5.17	352	5.1	7.2	10.2	16.2
30	8.25	441	6.5	9.2	13.0	21.0
31	12.95	550	8.2	11.6	16.4	26.0
32	20.71	682	10.6	14.9	21.0	34.0
33	30.60	828	12.7	18.2	26.0	41.0
34	50.95	1078	16.5	23.0	33.0	52.0
35	83.92	1392	21.0	30.0	42.0	67.0
36	112.00	1500	26.0	37.0	52.0	83.0

- ¹ Continuously pulsed at stated watts and duty cycle
- ² Single pulse at stated watts (with coil at ambient room temperature 20°C)
- ³ Other coil awg sizes available — please consult factory
- ⁴ Reference number of turns

Specifications


Dielectric Strength	1000 VRMS
Recommended Minimum Heat Sink	Maximum watts dissipated by solenoid are based on an unrestricted flow of air at 20°C, with solenoid mounted on the equivalent of an aluminum plate measuring 3" square by 1/8" thick
Coil Resistance	25-35 awg, ±5%; 36 awg, ±10%
Weight	1.50 oz (42.5 gms)
Holding Force	5.4 lb (24.0 N) @ 105°C
Dimensions	Ø1.000" x 0.530" L (See page 31)

How to Order


Add the coil awg number (0XX) to the part number (for example: to order a 25% duty cycle unit rated at 6.5 VDC, specify 124910-027).

Please see www.ledex.com (click on Stock Products tab) for our list of stock products available through our North American distributors.


- Well-suited for battery operation. See the "Battery Operated Solenoids" section for complete information.



Size 1EC — Typical Force @ 20°C



Size 1EC— Typical Speed @ No Load, 20°C



Force values for reference only.


All specifications subject to change without notice.

Ledex® Low Profile Dimensions


Inches (mm)

All solenoids are illustrated in energized state


Size 0EC



Size 1EC



Size 2EF/2EC



All solenoids are illustrated in energized state

All specifications subject to change without notice.