

ABOUT KEYSTONE ELECTRONICS

CUSTOM CAPABILITIES

VIEW DYNAMIC PDF CATALOG

PART BUILDER SYSTEM

CALENDAR OF EVENTS

NEWS, ADS AND VIDEOS

DISTRIBUTOR LOCATOR

ON-LINE ORDERING

CHECK DISTRIBUTOR STOCK

PRODUCT CATALOG:

ALL PRODUCT CATEGORIES

BATTERY & COIN CELL HOLDERS,
CONTACTS & CLIPSBRACKETS (COMPUTER &
MOUNTING)ELECTRONIC HARDWARE &
ACCESSORIES

FUSE CLIPS & FUSE HOLDERS

HANDLES FOR INSTRUMENTATION

LED SPACERS & LENS CAPS

PLUGS, PINS, JACKS & SOCKETS

QUICK-FIT TERMINALS

SCREW TERMINALS & TERMINAL
BLOCKS

SCREWS & PANEL HARDWARE

SPACERS & STANDOFFS

TERMINALS & TERMINAL BOARDS

TEST POINTS, TIPS, PROBES,
JUMPERS AND CLIPS

ISO 9001:2008 CERTIFIED

ROHS COMMITMENT

REACH DECLARATION

CONFLICT MINERALS DECLARATION

DISTRIBUTOR LOG-IN CENTER

PRODUCT WARRANTY INFORMATION


6-32 Threaded Female Standoffs

[Spacers & Standoffs](#) » [Standoffs, Hex & Round](#) »

Hex & Round Standoffs

6-32 Threads

- .250 [6.35] O.D. -
- Brass • Aluminum • Stainless Steel • Nylon • Phenolic



HEX O.D.	HEX					LENGTH		ROUND			ROUND O.D.
	NYLON V2	NYLON V0	STAINLESS	BRASS	ALUM	IN.	MM	BRASS	ALUM	PHENOLIC	
			CAT. NO.	CAT. NO.	CAT. NO.			CAT. NO.	CAT. NO.	CAT. NO.	
.250 [6.3]	1903A	8441A	1922	1451A	2208	.250	[6.4]	1548A	3485	383	.250 [6.3]
	1903B	8441B	1922A	1451B	2209	.375	[9.5]	1548B	3486	384	
	1903C	8441C	1922B	1451C	2210	.500	[12.7]	1548C	3487	385	
	1903F	8441D		1451D	1813	.625	[15.9]	1548D	1847		
	1903D	8441E	1922C	1451E	2211	.750	[19.1]	1548E	3488	386	
	1903G	8441F		1833	1816	.875	[22.2]	1879	1848		
	1903E	8441G	1922D	1635	2212	1.000	[25.4]	1548F	3489	387	
				1636	1818	1.250	[31.8]	1881	1853		
			1922E	1637	2213	1.500	[38.1]	1882	3490	388	
				1638	1819	1.750	[44.5]	1883	1855		
			1922F	1639	2214	2.000	[50.8]	1884	3491	389	
				1642	1820	2.250	[57.2]	1885	1856		
			1643	1825	2.500	[63.5]	1886	1857			

Other O.D's and sizes available - visit our [Part Builder System](#) for additional productsProducts: [Show/Hide Product View](#)