

## Product Details for 252HX



### 252HX

Tyco Part Number: 5-1618071-1

[Active](#)

## Sensors, Monitors & Protective Relays

[Not ELV or RoHS Compliant](#)

### Product Highlights:

- ? [250 Series](#)
- ? [Protective Relay](#)
- ? [AC Actuating System](#)
- ? [Input Voltage = 115 VAC](#)
- ? [Over/Undervoltage Protection Function](#)

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us](#)
- [About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

? [None Available](#)

#### Catalog Pages/Data Sheets:

? [None Available](#)

#### Product Specifications:

? [None Available](#)

#### Application Specifications:

? [None Available](#)

#### Instruction Sheets:

? [None Available](#)

#### CAD Files:

? [None Available](#)

#### Additional Information:

? [Product Line Information](#)

#### Additional Product Images:

? [Line Drawing](#)

#### Related Products:

? [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

? [Product Type](#) = Protective Relay

#### Electrical Characteristics:

- ? [Actuating System](#) = AC
- ? [Input Voltage \(VAC\)](#) = 115
- ? [Phase](#) = Three
- ? [Contact Rating](#) = 5A Resistive @ 120 VAC

#### Body Related Features:

? [Series](#) = 250

#### Configuration Related Features:

- ? [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- ? [Contact Arrangement, Additional Output](#) = 1 Form B, SPST-NC, 1 N/C

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Operation/Application:

- ? [Protection Function](#) = Over/Undervoltage
- ? [Time Delay](#) = Without

#### Other:

? Brand = CII