




TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

+ RELAYS, CONTACTORS & SWITCHES

HIGH VOLTAGE RELAYS



✓ Active

TE CONNECTIVITY (TE)

EV202MSAND=RELAY, EV202 DPST-NO, 28V

Kilovac

5-1618407-3

TE Internal Number: 5-1618407-3

Always EU RoHS/ELV Compliant

Contact Arrangement **2 Form X, DPST-NO**

High Voltage Connection (Coil) **Flying Leads**

High Voltage Connection (Power) **Screw Terminals**

Economizer **Internal**

Auxiliary Contacts **With**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

RF Rated	No
Product Type	Relay
Relay Type	High Voltage

Configuration Features

Economizer	Internal
------------	-----------------

Electrical Characteristics

Voltage (Max) (VDC)	900
Coil Voltage Rating (VDC)	28

Contact Features

Contact Arrangement	2 Form X, DPST-NO
Auxiliary Contacts	With
Contact Current Rating (A)	350

Termination Features

High Voltage Connection (Coil)	Flying Leads
High Voltage Connection (Power)	Screw Terminals

High Voltage Connection Length

390 mm [15.3 in]

Termination Style

Screw Terminals

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

Customers Also Bought

BUS BAR CONNECTORS	SURFACE MOUNT RESISTORS	SURFACE MOUNT RESISTORS	HIGH VOLTAGE RELAYS
			
<p>AMP PDS BUSPLUG 125F3 SER 213647-1</p>	<p>CPF 0805 6K2 0.1% 25PPM 1K RL CPF0805B6K2E1</p>	<p>RP 2B 200K 0.1% 15PPM CUT LENGTH RP73D2B200KBTG</p>	<p>EV200HAANA=RELAY, SPST-NO WITH EV200HAANA</p>