



Select a Category

GO

WIRE STRIPPER/CUTTER - SOLID AND STRANDED WIRE

[Product Index](#) > [Strippers, Cutters, Crimpers](#) > [Wire Strippers/Cutters](#) > [Wire Stripper/Cutter - Solid and Stranded Wire](#) > 1011

Wire Stripper-Cutter - Solid and Stranded Wire

- Strips six standard wire sizes without nicking wire.
- Scissors action of 1/2" (13 mm) wide cutter makes clean cuts with little effort.
- Serrated nose jaws to bend, shape, or pull wire: holes for looping wire ends.
- Spring-loaded for self-opening action.
- Comfortable, plastic-covered handles.



Buy Now!



Pictured: 1011

Cat. No.	Handle Color	Overall Length	Strips and Cuts	Weight (lbs.)
1011	blue	6-1/8" (156)	10 - 20 AWG solid & stranded (4.0 - 0.50 mm ²)	.23

All dimensions are in inches and (millimeters) except where indicated.

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .eps photo](#)



Back

The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

▲ WARNINGS: Always wear approved eye protection.

▲ WARNINGS: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).