



Home » Catalog » Insulated Tools » Insulated Screwdrivers » Insulated Cabinet-Tip - Round-Shank

Insulated 3/8" (10 mm) Cabinet-Tip 8" (203 mm) Round-Shank Screwdriver



Cat. No. 602-8-INS

Product Features

- 1000V Rated for safety.*
- Durable, two-layer, molded insulation to meet or exceed all ASTM and IEC standards for insulated tools.*
- Custom US-made tool steel.*
- Cushion-Grip handle for superior torque and comfort.*
- Made in the USA.*
- This sku replaces 602-10-INS.*

BUY NOW

FIND RETAILER



Specifications

Video

Downloads

Warnings

Overall Length: 13-3/8" (340 mm)

Shank Length: 8" (203 mm)

Shank Tip Width: 3/8" (10 mm)

Weight (lbs.): .52

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

