



Tool Online Catalog

WHERE TO BUY

Select a Category

GO

POWER-RETURN STEEL RULES - HIGH-VISIBILITY CASE

[Product Index](#) > [Levels and Measuring Tools](#) > [Power-Return Rules](#) > [Power-Return Steel Rules - High-Visibility Case](#) > 928-25HV

25' Power-Return Steel Rule - High-Visibility Case

- Same as No. 922 Series, but with high-visibility case.
- High-visibility, high-impact orange case makes it easy to find in a tool box, pouch, and on the jobsite.
- 16" (406 mm) and 19.2" (485 mm) stud-center marks.
- Tape measure holders available.



Buy Now!

Pictured: 928-25HV

Line Art: 928-25HV

Cat. No.	Case Color	Length	Weight (lbs.)	Width
928-25HV	Hi-Viz Orange	25' (7.5) m	1.00	1" (25)

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .jpg lineart

Download High-Resolution .eps photo

Download High-Resolution .eps lineart



Back

The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

⚠ WARNINGS: Always wear approved eye protection.

⚠ WARNINGS: Never use on or near live electrical circuits.

⚠ WARNINGS: Do NOT open the case. Spring motor is under tension, and opening case may cause injury.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).