



Select a Category

GO

**JOURNEYMAN™ HIGH-LEVERAGE SIDE-CUTTING PLIERS**

[Product Index](#) > [Journeyman™ Series](#) > [Journeyman™ Pliers](#) > [Journeyman™ High-Leverage Side-Cutting Pliers](#) > J2000-9NE

**9" Journeyman™ High-Leverage Side-Cutting Pliers - Heavy-Duty Cutting**



- 2000 series cuts ACSR, screws, nails and most hardened wire.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Streamlined design with sure-gripping, cross-hatched knurled jaws.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.
- Features combination polished and black-oxide finish.



**Buy Now!**

*Pictured: J2000-9NE*

*Line Art: J2000-9NE*

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Knife Length	Nose Type	Overall Length	Weight (lbs.)
J2000-9NE	light-blue/black	Journeyman	1-19/32" (41)	5/8" (16)	1-1/4" (32)	25/32" (20)	New England	9-1/2" (241)	1.13

*All dimensions are in inches and (millimeters) except where indicated.*

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .jpg lineart](#)

[Download High-Resolution .eps photo](#)

[Download High-Resolution .eps lineart](#)



*The downloadable files are compressed in .zip format to save on downloading times.  
Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.*

**⚠ WARNINGS:** Always wear approved eye protection.

**⚠ WARNINGS:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

---

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).