

6" Diagonal Cutting Pliers Tapered Nose



ENLARGE

Cat. No.D202-6

Product Features

- ▶ Easy working in confined areas.
- ▶ Short jaws and beveled cutting edges permit close cutting of wire.
- ▶ Induction-hardened cutting knives for long life.
- ▶ Hot-riveted joint ensures smooth action and no handle wobble.
- ▶ Plastic-dipped handles for comfort and ease of identification.
- ▶ Custom, US-made tool steel.

BUY NOW

FIND RETAILER

Specs

Downloads

Warnings

Accessories

Buy Now

Overall Length: 6-1/8" (155.6 mm)

Jaw Width: 11/16" (17.5 mm)

Cutting Knives: Standard

Handle Color: Red

Cut Style: Standard

Handle Length: 4-15/16" (125.4 mm)

Handle Type: Curved

Jaw Capacity: 1/2" (12.7 mm)

Material: Steel

Tether Capable: No

Jaw Length: 13/16" (20.6 mm)

Jaw Thickness: 7/16" (11.1 mm)

Handle Finish: Plastic-Dipped

Weight: 0.29 lbs. (0.13 kg)

Finish: Combination Polished Black Oxide

Handle Material: Steel

Insulated: No

Joint Type: Hot Riveted

Nose Type: Tapered

Type: Diagonal Cutting