



Home » Catalog » Pliers » Diagonal-Cutting Pliers » High-Leverage Diagonal-Cutting Pliers - Angled Head

## Diagonal Cutting Pliers High Leverage



ENLARGE

### Cat. No.D248-8

#### Product Features

- ▶ Angled head design for easy work in confined spaces.
- ▶ High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.
- ▶ Short jaws and beveled cutting edges permit close cutting of wire.
- ▶ Induction-hardened cutting knives for long life.
- ▶ Hot-riveted joint ensures smooth action and no handle wobble.
- ▶ Plastic-dipped handles for comfort and ease of identification.
- ▶ Custom, US-made tool steel.



**BUY NOW**

**FIND RETAILER**



**Specs**

Downloads

Warnings

Accessories

Related Items

Buy Now

**Overall Length:** 8-1/16" (204.8 mm)

**Jaw Width:** 1-3/16" (30.2 mm)

**Cut Style:** Standard

**Handle Color:** Red

**Finish:** Combination Polished Black Oxide

**Handle Material:** Steel

**Head Type:** Angled

**Jaw Capacity:** 3/4" (19.1 mm)

**Material:** Steel

**Type:** Diagonal Cutting

**Jaw Length:** 13/16" (20.6 mm)

**Jaw Thickness:** 7/16" (11.1 mm)

**Handle Finish:** Plastic-Dipped

**Weight:** 0.60 lb (0.27 kg)

**Handle Length:** 6-3/4" (171.5 mm)

**Handle Type:** Handform

**Insulated:** No

**Joint Type:** Hot Riveted

**Tether Capable:** No