



Home » Catalog » Test & Measurement » Electrical Testers

# GFCI Receptacle Tester

**Cat. No. RT210**

## Product Features

- ▶ Conforms to UL Std 1436, Certified to CSA Std C22.2 #160.
- ▶ Built to withstand a 6.6 ft. (2m) drop.
- ▶ Operating temp: 32°F to 140°F (0°C to 40°C).
- ▶ Works on GFI outlets and confirms operation of the ground fault.
- ▶ Nominal Voltage: 110/125V AC at 50/60Hz in 3-wire outlet.



ENLARGE +



Buy Now

Find Retailer



Specs

Video

Downloads

Warnings

Buy Now

**Drop Protection:**

6.6 ft. (2 m)

**GFCI:**

Yes

**Voltage Range:**

110/125V AC at 50/60Hz in 3-Wire Outlet

**Weight (oz.):**

1.3