

## Hi-Viz Diagonal Cutting Pliers Angled



ENLARGE

### Cat. No.D248-8-GLW

#### Product Features

- ▶ *Glow in the dark grips to easily locate your tool in dark or low lit areas.*
- ▶ *Grips charge in natural and artificial lighting.*
- ▶ *Angled head design for easy work in confined areas.*
- ▶ *High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.*
- ▶ *Short jaws and beveled cutting edges permit close cutting of wire.*
- ▶ *NOTE: Glow time and intensity may vary if charged in low light. Clean grips regularly to maintain glow brightness.*

**BUY NOW**

**FIND RETAILER**



**Specs**

Video

Downloads

Warnings

Accessories

Buy Now

**Overall Length:** 8-1/16" (204.8 mm)

**Jaw Width:** 1-3/16" (30.2 mm)

**Cut Style:** Standard

**Handle Color:** Glow

**Finish:** Combination Polished Black Oxide

**Handle Material:** Steel

**Head Type:** Angled

**Jaw Capacity:** 3/4" (19.1 mm)

**Material:** Steel

**Type:** Diagonal Cutting

**Jaw Length:** 13/16" (20.6 mm)

**Jaw Thickness:** 7/16" (11.1 mm)

**Handle Finish:** Plastic-Dipped

**Weight:** 0.60 lbs. (0.27 kg)

**Handle Length:** 6-3/4" (171.5 mm)

**Handle Type:** Handform

**Insulated:** No

**Joint Type:** Hot Riveted

**Tether Capable:** No