

Home » Catalog » Insulated Tools » Insulated Screwdrivers » Insulated Phillips

Screwdriver, Insulated, #3 Phillips Tip, 7" Shank

Cat. No. 6337INS

Product Features

- ▶ 1000V Rated for safety.
- ▶ Durable, two-layer, molded insulation to meet or exceed all ASTM and IEC standards for insulated tools.
- ▶ Cushion-Grip handles for greater torque and comfort.
- ▶ Custom US-made tool steel.
- ▶ Made in the USA.
- ▶ This sku replaces 603-6-INS.



ENLARGE (+)

Buy Now

Find Retailer



Specs

Video

Downloads

Warnings

Buy Now

Application:

For Work Near Energized Sources

Handle Material:

High-Dielectric Plastic

Insulated:

Yes

Protection:

1000V

Shank Shape:

Round

Standard:

IEC 60900 and ASTM F1505

Tip Type:

Profiliated Phillips

Weight (lbs.):

.40

Blade Material:

Induction Hardened Steel

Handle Type:

Dual Insulated

Overall Length:

12-3/8" (314 mm)

Shank Length:

7" (178 mm)

Special Features:

Flame Retardant and Impact Resistant Handle

Tip Size:

#3

Weight:

0.40 lbs.