

2713-B

30 Amp, 125/250 Volt, NEMA L14-30R, 3P, 4W, Locking Connector, Industrial Grade, Grounding, All Black - BLACK

Leviton's industry leading locking devices, such as our Black & White line of industrial grade plugs and connectors and receptacles, offer superior performance, long lasting reliability and other features that are backed by a lifetime warranty.



UPC Code : 078477143599

Country Of Origin : United States



Available Colors :



Technical Information

AC Horsepower Ratings

At Rated Voltage : 2 HP L-L / 2 HP L-N

Electrical Specifications

Amperage : 30 A

Current Interrupting : Certified for current interrupting at full rated current

Dielectric Voltage : Withstands 2000V per UL498

Grounding : Grounding

Pole : 3

Temperature Rise : Max 30C after 250 cycles OL at 200 percent rated current

Voltage : 125/250 VAC

Wire : 4

Environmental Specifications

Environment : Dry

Flammability : Rated HB or better UL94

Operating Temperature : -40°C to 60°C

Material Specifications

Assembly Screws : Steel, Zinc Plated

Back Cover : Thermoplastic

Blades/Contacts : Solid Brass

Body Material : Impact Modified Nylon

Clamp Insert : Nylon

Color : Black

Cord-Clamp : Nylon

Terminal Screws : Brass

Wire Module : Nylon

Mechanical Specifications

Cord Range : .595 - 1.150

Product ID : Ratings are permanently marked on device

Terminal Accom. : 18-10 AWG

Terminal ID : Brass-Hot, Green-Ground, Silver-Neutral

Wire Gauge : 14-8 AWG

Product Features

Brand : Black and White

Color : Black

Device Type : Locking Connector

NEMA : L14-30R

Standards and Certifications

ANSI : C-73

CSA C22.2 No. 42 : File LR-406

NEMA : WD-6


NOM : 057

UL Fed Spec WC-596 : File E13393


UL498 : File E13393

Warranty : Limited Lifetime Warranty

Dimensional Diagram



Wiring Diagram



SPECIFICATION SUBMITTAL

JOB NAME: <input style="width: 95%;" type="text"/>	CATALOG NUMBERS: <input style="width: 95%;" type="text"/>
JOB NUMBER: <input style="width: 95%;" type="text"/>	<input style="width: 95%;" type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

