AQUILINE FOOT SWITCH





Engineered with an eagle eye on quality and value, the AQUILINE foot switch from Linemaster soars above the rest. With the choice of SPDT, DPDT, or two-stage operation, the patented AQUILINE

LINEMASTER Switch Corporation Tel (860) 974-1000 is a versatile solution for applications requiring a precision lightweight or medium weight foot control. Form follows function in the AQUILINE's graceful curves and patented design, while a non-skid base pad and raised treadle ribs ensure positive performance.

29 Plaine Hill Road, P.O. Box 238 Fax (860) 974-0691 The AQUILINE foot switch is available in reinforced polymeric material or metal. Of course you can always count on the famous consistency and familiar action you get with every Linemaster switch. Only from Linemaster -American made innovation at work.

Woodstock, CT 06281-0238 USA Toll-Free Fax (800) 974-3668 US Only

www.linemaster.com/ds/aquiline/

AQUILINE Foot Switch

Its Got the Look and the Touch



0

Features:

Easy to Operate - Press and hold on actuation

SPDT, DPDT, or Two-Stage Operation. Two-Stage applications are only available in the metal version

Rustproof and corrosion proof reinforced polymeric material for light duty applications

*** ***

Available to IP68 degree of protection and CE marked

Available in multi-pedal versions

Non-skid base pad and raised ribs on cover for positive traction during operation

**(

Attractive non-glare finish. Custom colors, and color matching available with quantity orders

*** * ***

Integrated adjustable strain relief clamp

Full and oversized guards available



062 IN. (2.08mm) DIA. MOUNTING HOLES (2 PLACES) 2.562 IN. (65.07mm) 3.999 IN. (101.32mm)

NOTE: ALL DIMENSIONS ARE FOR REFERENCE ONLY.

EN 60529 Approvals **Catalog Number** Description Color Circuit Form **Electrical Ratings** c**₩**us (€ IP20 971-S Polymeric / Momentary SPDT C Dark Grav c**₩**us (€ IP20 971-SA Polymeric / Momentary Light Gray SPDT С 15 A 125-250 VAC IP20 971-SB Polymeric / Momentary Blue SPDT С 1/2 H.P. 125-250 VAC c**₩**us (€ С IP20 971-SO SPDT Polymeric / Momentary Orange c**₩**us (€ IP20 Polymeric / Momentary SPDT С 971-SY Yellow c**₩**us (€ IP68 971-SWNO2101 Polymeric / Momentary Dark Gray SPST-Wired NO Α 3 A 25 VAC c**¶∐**us (€ IP68 971-SWNO210A1 Polymeric / Momentary SPST-Wired NO Α Light Gray c**₩**us (€ IP20 971-SC26² SPDT-Wired NO Polymeric / Momentary Dark Gray Α 10 A 125-250 VAC c**₩**us (€ IP20 971-SC26A² Polymeric / Momentary SPDT-Wired NO Α 1/2 H.P. 125-250 VAC Light Gray c**₩**us (€ с IP20 974-S DPDT Polymeric / Momentary Dark Gray c**₩**us (€ IP20 974-SA Polymeric / Momentary Light Gray DPDT С 15 A 125-250 VAC c**₩**us (€ SPDT 1/2 H.P. 125-250 VAC IP20 971-SM Die Cast Zinc / Momentary Black с c**₩**us (€ IP20 972-S* Die Cast Zinc / Momentary 2-Stage Black SPDT Each Stage С IP20 TWIN 971-SMC48³ Die Cast Zinc / Momentary Black SPDT-Wired NO Α 13A 125-250 VAC; 1/2 H.P 125-250 VAC Die cast metal housing. 1 Meets IP68 & is supplied with 10 ft. 18/2 cord without plug.

²Supplied with 6 ft. 18/2 cord without plug. ³Die Cast Metal Housing; Supplied with 8 ft. 16/4 cord without plug, green lead grounded.

LINEMASTER Switch Corporation Tel (860) 974-1000 29 Plaine Hill Road, P.O. Box 238 Fax (860) 974-0691 Woodstock, Connecticut 06281-0238 USA Toll-Free Fax (800) 974-3668 US Only

www.linemaster.com/ds/aquiline/

SPECIFICATIONS