

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com[All Categories](#) > [Clipper Foot Switch](#) > Item # 642-S**Item # 642-S, Clipper Foot Switch****WIDE TREADLE**[larger image](#)

The rugged, long life clipper switch models have proved themselves in the field over many years of usage. All maintained models offer "Push on Push Off" action through a molded nylon actuating cam mechanism that insures long trouble-free performance. The wide treadle models offer a large seven inch target for the operator's foot. Cast iron housing. Nonskid base pad. Complete with adjustable strain relief connector. Black finish.

Specifications

Style/Series	Wide Treadle
Description	Momentary
Circuit	SPDT
Form	C
Electrical Rating	20 A 125-250 VAC 1 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20
Size	4 1/2 x 3 1/2 x 1 1/2 Inch
Weight Approx.	2 1/4 lbs

[Print](#)[Back](#)