



- Product Line**
- ZConnect
 - Ceres Connectors
 - X-Lok Connectors
 - M Series Sensor Connectors**
 - > MPronto-12
 - > M8
 - > M10.5
 - > M12
 - > M20
 - > M23
 - > Distribution Box
 - > Guided M8
 - FLOS & FLOS+ Connectors
 - Power Connectors
 - RBL Connectors
 - HS-Lok Connectors
 - NMEA 2000 Connectors
 - RJ Connectors
 - USB Connectors
 - D-SUB Connectors
 - SSL Solution Connectors
 - HDMI Connectors
 - DVI Connectors
 - Fiber Optic Connectors
 - Cable Joiner
 - FICX Connectors
 - Cable Gland - Anti-UV
 - Vent
 - LED Indicator
 - CNC Products
- Product Applications**
- Product Search**

Home > Product Line > M Series Sensor Connectors > M12

☆ Bookmark | Share | Print



Part Number : M12A-04BFFA-SL8001

Share 0 | Tweet

Pin : Copper Alloy,Gold Plated

Connector Body : Thermoplastic, UL Recognized.;Zn Alloy ,Nickel Plated

Temperature Range : -40°C~105°C

Download:

- Sample 3D model(.stp)
- Sample 3D model(.igs)

Add to inquiry list | Check inquiry list | Submit inquiry

| Description | Details |
|---------------------|----------------------------|
| Connector | M12 A Code |
| Connector Gender | Female connector |
| Mating Style | Screw Thread |
| Current Rating | 4A |
| No. of Contacts | 4 pins |
| Contact Gender | Female pin |
| Field installable | Field Installable (Solder) |
| Connector body type | Without strain relief |
| Backshell | Straight |
| Waterproof Rating | IP68 |
| Cable OD Φ | 4.5~6.5 |
| Voltage rating | 250V AC/DC |

* Design and specifications are subject to change without notice. update: 2021-03-02 00:00:00

