


## 010 - 0081 - 0000 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



### SMB RF Connectors

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Housing Crimp Tool
- ? Jack, Plug
- ? Miniature
- ? Terminate To Coaxial Cable
- ? Coupler Style = Threaded

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

**010 - 0081 - 0000**  
(4 - 1532129 - 4)  
 [Active](#)

### Documentation & Additional Information

#### Product Drawings:

? None Available

#### Catalog Pages/Data Sheets:

? None Available

#### Product Specifications:

? None Available

#### Application Specifications:

? None Available

#### Instruction Sheets:

? None Available

#### CAD Files:

? None Available

#### Additional Information:

? [Product Line Information](#)

#### Related Products:

? [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Housing Crimp Tool
- ? [Gender](#) = Jack, Plug
- ? Connector Series = Miniature
- ? [Grade](#) = Commercial

#### Termination Related Features:

? [Coaxial Cable Termination Type](#) = Crimp

#### Body Related Features:

- ? Coupler Style = Threaded
- ? [Body Plating](#) = Gold per MIL -G-45204, Type II, Grade C, Class 1
- ? Cable Jacket Diameter (mm [in]) = 2.24 [0.088]

#### Contact Related Features:

- ? [Center Contact Plating](#) = Gold per MIL -G-45204, Type II, Grade C, Class 1
- ? Contacts = With

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

? [Terminate To](#) = Coaxial Cable

#### Other:

? Brand = Microdot