

Proheat® 1000 Quick-Touch™ Heat Gun



CALL US: 1.800.558.9413

[Ask A Question](#)

[Request A Catalog](#)

[View/Print Catalog](#)

[Receive Master Updates](#)

[Where To Buy](#)

SHARE THIS PAGE



Features

Videos

Support Materials

Attachments/Accessories

Replacement Parts

Quick-touch heat gun with momentary contact switch

- Compact, lightweight, easy-to-use
- Balanced ergonomic design prevents operator fatigue
- Protective hand/switch guard and hanging loop
- Momentary Contact Switch – if not held, unit is off
- Use to activate adhesives, bend plastics, dry filler material, shrink tubing and more

- ⌵ Models
- ⌵ Specifications

Available Models

MODEL NO.	DESCRIPTION
PH-1000	Proheat Quick-Touch Heat Gun with Momentary Contact Switch, 1000°F /540°C, 120V, 60 Hz, 11A, and 1300W
PH-2000	Proheat Heat Gun with Momentary Contact Safety Switch, 1000°F /540°C, 230V*, 50/60 Hz, 6.2A, 1426W, CE

Specifications

Avg. Temp. 1000° F (540° C)  
 Avg. Air Volume: 16 CFM/453 l/min  
 Avg. Air Velocity: 4000 FPM/1219m/min  
 Motor: Permanent Magnet  
 Dimensions: 8.2" L x 3.0" W x 7.3" H

Nozzle Opening: 1.3" Dia.  
 Cordset: 6 ft., 3-wire grounded  
 Net Weight - Single Unit: 1.6 lbs.  
 Shipping Weight - Single Unit: 2 lbs.



