

Magnecraft

191 Waukegan Rd, Ste 206

Northfield, IL 60093-2743

Phone: (847)441-2526

Fax: (847)441-2522


Email: info@magnecraft.com

Item # 70-788EL11-1, 70-788EL11-1 Socket / 25 Amp Rating, 300 Volts

70-788EL11-1 Socket / 25 Amp Rating, 300 Volts

11 Pin Logic Style, Finger Safe, DIN Mount, Elevator Terminals, Module Compatible

This Item is Normally Stocked



[SPECIFICATIONS](#) · [ELECTRICAL RATING](#) · [DIELECTRIC STRENGTH](#) · [TEMPERATURE](#) · [CONSTRUCTION](#) · [MISCELLANEOUS](#)

SPECIFICATIONS

Contact Configuration	Triple Pole
Mounting Style	DIN Mount
Rated Current	25 A
Number of Terminals	11

ELECTRICAL RATING

Nominal Voltage Rating	300 V
Nominal Current Rating	25 A

DIELECTRIC STRENGTH

Output to Adjacent Output Terminals	3000 V (rms)
Output to Input Terminals	3000 V (rms)
Terminals to Rail / Chassis	3000 V (rms)

TEMPERATURE

Operating Range	- 40 to + 80 °C
Storage Range	- 40 to + 105 °C

CONSTRUCTION

Protection Category (Finger Safe), EN 60529	IP 20
Internal Metal Tracks	Copper Alloy Zinc Plated
Screw Terminals	Steel Zinc Plated
Screw Style	Combination Head
Screw Size	M3.5 mm
Screw Torque 3.5 mm (Maximum)	9 / 1.0 Lb-in / Nm

MISCELLANEOUS

Socket Mounting	Din
Wire Size Capacity (Maximum), EN 60204-1, Solid Cu	10 / 14 (2) AWG, 6 / 2.5 (2) mm ²
Wire Size Capacity (Maximum), EN 60204-1, Stranded Cu	10 / 14 (2) AWG, 6 / 2.5 (2) mm ²
Wire Connection Method	Elevator
DIN Rail Mounting, EN 60715	35 mm
Flammability Rating	94V-0 Class
Body Color	Light Gray
DIN Locking Method	Red Plastic Locking Clip
Product Certification	CSA UL
Conformance	CE RoHS