



Better. By Design.

800.238.7474 ▪ [contact](#) ▪ [where to buy](#)



[products](#) [resources](#) [technical support](#) [industry solutions](#) [blog](#)

[Home](#) : [Search](#)

Search results for TE-8812U

Not what you're looking for? [Search the entire site for TE-8812U.](#)

OVERVIEW

[Details](#)


[Stock Status](#)

[Contact](#)

[Print](#)

[Share](#)

TE-8812U



May not be exact product—for reference only.

Family:

TIME DELAY RELAY

Function:

MULTI-FUNCTION

Timing Range:

0.1 sec - 10 days

Input Voltage:

12-240V AC/DC

Output:

15A DPDT

Files

- [Catalog](#)
- [Instruction Sheet](#)
- [2D/3D CAD Drawing](#)

©2019 Macromatic Industrial Controls, Inc.

W134N5345 Campbell Drive
Menomonee Falls, WI 53051

800-238-7474 • 262-781-3366



[Rep Login](#) | [Newsletter Sign Up](#) | [Articles](#) | [Employment](#) | [Privacy Policy](#) | [Sitemap](#)
[Knowledgebase General](#) | [Alternating Relays](#) | [Current Sensing Relays](#) | [Liquid Level Control Relays](#) | [Seal Leak Relays](#) | [Three-Phase Monitor Relays](#) | [Time Delay Relays](#) | [Voltage Monitor Relays](#)

